

Leveling Mount

Standard

NFJN
NFJNS
NFJNF
(Stainless Steel)

M	D	l ₁	l ₂	E	B	t
5	30	3.5	4	5.4	8	1.6
6		4	5		10	
8	38	5.5	6.5	11	13	
10		7	8		17	
12	60	8	10	18	19	
16		10	13		24	2.0
20	75	13	16	20	30	

Type	M Material	S Surface Treatment
NFJN	SS400	Trivalent Chromate
NFJNF	Equivalent	Trivalent Chromate
NFJNS	SUS304	Electrolytic Polishing

RoHS10

Screw shafts can turn independently of a base and can tilt 3 to 5 degrees.

A Selectable

Part Number	M-A	L	Allowable Vertical Load (kN)	Mass (g)	Unit Price	
					NFJN / NFJNS	NFJN
5-30		40.5	1.5	15		
5-60		70.5		19		
6-40		51	2.1	21		
6-80		91		28		
8-50		68.1	3.9	50		
8-100		118.1		65		
10-75		94.6	4.3	88		
10-100		119.6		100		
12-50		78	4.9	142		
12-75		103		166		
12-100		128		184		
12-125		153		200		
12-150		178	5.9	219		
16-75		107		287		
16-100		132		317		
16-130		162		356		
16-150		182	8.8	383		
16-180		212		422		
20-100		135		493		
20-130		165		557		
20-150		185	605			
20-180		215	671			

A configurable in 10mm Increment

Part Number	M	A 10mm Increment	L	Unit Price
10		80-200	A+19.6	
12		80-250	A+28	
16		80-300	A+32	
20		110-300	A+35	

Tips of screws are painted.

Ordering Example

Part Number - A

NFJN12-100 - 80

NFJNF10 - 80

Alterations

Part Number - (WC, WK, SC, WN)

NFJN16-75 - WC

For NFJN only. No plating on alteration-applied sections. For alterations for 31 or more pieces, please request a quotation.

Alterations	Square Flats	Hex Flats	Wrench Flats	Hex Wrench Socket Machining
Code	WC	WK	SC	WN
Spec.	Ordering Code WC Applicable when 20 ≥ M ≥ 10	Ordering Code WK Applicable when 20 ≥ M ≥ 10	Ordering Code SC Applicable when 20 ≥ M ≥ 10	Ordering Code WN Applicable when 20 ≥ M ≥ 10
	M WC l	M WK l	M W l ₁ SC	M WN l
	10 6 10	10 6 10	10 8 8	10 4 5
	12 8 10	12 8 10	12 10 10	12 5 6
	16 10 12	16 10 12	16 13 10	16 5 6
	20 12 13.5	20 13 10	20 17 10	20 8 8

Leveling Mount

Non-Slip

Main Body	Type	① Main Body		② Rubber		M	D	l ₁	l ₂	E	B	H
		M Material	S Surface Treatment	M Material (Color)	H Hardness							
Steel Type	FJGN	SS400 Equivalent	Trivalent Chromate	Elastomer (Black)	-	8	45	5.5	6.5	15	13	6
	FJGM			Neoprene Rubber (Black)	-	10	7	8	17	6		
				Non-Migration Chloroprene Rubber (Grey)	Shore A70	12	8	10	23	19	7	
				Electrically Conductive Rubber (Black)	-	16	10	13	25	24	8	
				PVC (Dark Blue)	-	20	13	16	30	30		
Stainless Steel	FJGNS	SUS304	Electrolytic Polishing	Elastomer (Black)	-							
	FJGMS			Neoprene Rubber (Black)	Shore A70							
				Non-Migration Chloroprene Rubber (Grey)	-							
				Electrically Conductive Rubber (Black)	-							

Electrically Conductive Rubber Specific Volume Resistivity 10² ~ 10⁴Ω·cm

Screw shaft turns independently of the base and tilts slightly.

Part Number	FJGM / FJGMS	L	Allowable Vertical Load (kN)	Mass (g)	Unit Price							
					FJGN	FJGM				FJGNS	FJGMS	
Type	M-A	Rubber Material			R	C	D	S	FJGNS	R	C	D
8-50			70.5	50				-				
8-100			120.5	70				-				
10-75			97	91				-				
10-100			122	103				-				
12-75			106	178				-				
12-100*			131	196				-				
12-125*			156	212				-				
12-150			181	231				-				
16-75		R (Rubber)	110	301				-				
16-100*		C (Non-migration Chloroprene Rubber)	135	331				-				
16-130*		D (Electrically Conductive Rubber)	165	370				-				
16-150		S (PVC)	185	397				-				
16-180*			215	436				-				
20-100*			138	148				-				
20-130*			168	173				-				
20-150			188	194				-				
20-180*			218	220				-				

You cannot select the rubber material for FJGN and FJGNS. (Elastomer is used.) * PVC rubber applicable sizes

Ordering Example

Part Number - Rubber Material

FJGM16-75 - R