


ミスミ

HSS DRILLS

ハイス鋼ドリル

● ストレートシャンク / ロング -STRAIGHT SHANK / LONG LENGTH-

LSD



材質		直径D	公差 (h8)	シャンク径d	公差 (f11)			
		2 ~ 3	0 -0.014	2 ~ 3	-0.006 -0.066			
		3.1 ~ 6	0 -0.018	3.1 ~ 6	-0.010 -0.085			
仕様		6.1 ~ 10	0 -0.022	6.1 ~ 10	-0.013 -0.103			
		S形シンニング (無)  (有) ● シャンク径 (d) は直径 (D) と同じです。 ● ホモ処理 = 四三酸化鉄皮膜処理						
一般鋼 (SS・SCM)	合金鋼 (SCM)	鋼質鋼 (~45HRC)	高硬度鋼 (50HRC~)	工具鋼 (SKD, SKS)	ステンレス鋼 (SUS)	鋳鉄 (FC, FCD)	アルミ (Al)	銅 (Cu)
○	△			△		△	△	△

○=適 △=可

型番 LSD 1本単位

直径 D	溝長 ℓ	全長 L	¥通常単価 30本以上お見積り		
			1本	2~9本	10~29本
2	85	125	710	510	450
2.5	95	140	850	610	540
2.6	95	140	1,020	730	690
2.8	100	150	1,020	730	690
3	100	150	940	670	600
3.1	105	155	1,090	780	700
3.2	105	155	1,090	780	700
3.3	105	155	1,090	780	700
3.4	115	165	1,090	780	700
3.5	115	165	990	710	630
3.6	115	165	1,220	870	780
3.7	115	165	1,220	870	780
3.8	120	175	1,470	1,050	890
3.9	120	175	1,470	1,050	890
4	120	175	1,330	950	800
4.1	120	175	1,600	1,140	960
4.2	120	175	1,600	1,140	960
4.3	125	185	1,600	1,140	960
4.4	125	185	1,600	1,140	960
4.5	125	185	1,470	1,050	890
4.6	125	185	1,740	1,240	1,050
4.7	125	185	1,740	1,240	1,050
4.8	135	195	1,740	1,240	1,050
4.9	135	195	1,740	1,240	1,050
5	135	195	1,550	1,110	990
5.1	135	195	1,930	1,380	1,240
5.2	135	195	1,930	1,380	1,240
5.3	135	195	1,930	1,380	1,240
5.4	140	205	1,930	1,380	1,240
5.5	140	205	1,720	1,230	1,100
5.6	140	205	1,960	1,510	1,350
5.7	140	205	1,960	1,510	1,350
5.8	140	205	1,960	1,510	1,350
5.9	140	205	1,960	1,510	1,350
6	140	205	1,900	1,360	1,220
6.1	150	215	2,410	1,720	1,540
6.2	150	215	2,410	1,720	1,540
6.4	150	215	2,410	1,720	1,540
6.5	150	215	2,090	1,490	1,340
6.6	150	215	2,670	1,910	1,710
6.7	150	215	2,670	1,910	1,710
6.8	155	225	3,090	2,210	1,810
6.9	155	225	3,090	2,210	1,810
7	155	225	2,700	1,930	1,730
7.5	155	225	2,940	2,100	1,890
7.8	165	240	3,580	2,560	2,300
8	165	240	3,180	2,270	2,040
8.5	165	240	3,460	2,470	2,220
9	175	250	3,860	2,760	2,480
9.5	175	250	4,090	2,920	2,620
9.8	185	265	5,030	3,590	3,230
10	185	265	4,420	3,160	2,840



LSD 10  
型番 直径 (D)



巻末-3

切削条件 P.766

●ご希望によりPM6:00迄、当日出荷受付致します。